



YGS26 Compression Grounding Splice, 2/0 AWG Cu

By Burndy
Catalog # [YGS26](#)

HYGROUND® Grounding Irreversible Compression Splice;
Accommodates: 2/0 str.; 2.97" Length



Application

For Direct Burial In Earth Or Concrete

General

Connector Type	Splice
Construction Material - Main	Copper
Die Index	13
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YGS, Grounding Irreversible
UPC	781810220412
UPC 12 Digit	7818102204122

Dimensions

Dimension - B Length fraction	1-10/27 in
Dimension - B Length inch	1.45 in
Dimension - L Length Overall mm	80 mm
Dimension - Length Overall inch	3.13 in
Dimension - Outside Diameter inch	0.56 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	2/0 Str.
Conductor - Copper Str Size Range	2/0 Str.
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">UL467UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B;UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	9600

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YGS_LineArt](#)
[Sales Drawings - SD..082514-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YGS26-SPEC-EN | REV 5/2024