



YGS2C Compression Grounding Splice, 2 AWG Cu

By Burndy
Catalog # YGS2C



HYGROUND® Grounding Irreversible Compression Splice;
Accommodates: #2 Str.; 2.41" Length.

General

Catalog Number	YGS2C
Color Code	Brown
Connector Type	Splice
Die Index	10
Material	Copper
Physical Attribute - Number of	2
Crimps Required	
Plated	N
Plating Type	Unplated
Trade Name	HYLINK™
Type	Splices
UPC	781810220405
UPC 12 Digit	7818102204055

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.22 in
Dimension - L Length Overall mm	68 mm
Dimension - Length Overall inch	2.67 in
Dimension - Outside Diameter inch	0.42 in

Conductor Related

Conductor - Copper Solid Size	2
Conductor - Copper Solid Size Range	2
Conductor - Copper Str Size	2 Sol./Str.
Conductor - Copper Str Size Range	2 Sol./Str.
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">UL467UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B;UL467
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	11600

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YGS_LineArt](#)
- [Sales Drawings - SD..082514-01](#)
- [Specifications - YGS2C](#)



A Hubbell brand