



YGT275WOCC Static Grounding Receptacle

By Burndy
Catalog # [YGT275WOCC](#)



Static Grounding Receptacle without cap to provide permanent corrosion proof grounding point using suitable YGHR or YGLR or YGHP connectors.

General

Connector Type	To be connected to suitable YGHR or YGLR or YGHP
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	HYGROUND®
UPC	781810096055
UPC 12 Digit	7818100960555

Dimensions

Dimension - D inch	2.75 in
Dimension - Ground Rod Size	3/4
Dimension - Height fraction	5-1/2 in
Dimension - Height inch	5.50 in

Conductor Related

Conductor - Rod Size	3/4 in
Conductor - Rod Size Range	3/4 in
Conductor Type	Rod-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Sales Drawings - SE208023-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YGT275WOCC-SPEC-EN | REV 8/2023