

YH298CWC, Compression H-Tap

By Burndy
Catalog # [YH298CWC](#)

Copper Compression H Tap, Tin Plated, Accommodating the following wire sizes - Run (Main): 250 kcmil-2 AWG Class B,C, 4/0 AWG-2 AWG Class I, DLO; Tap 1: 8 AWG-14 AWG Class B, C, 8 AWG-14 AWG Class G,H,I, DLO, 8 AWG Class K, Tap 2: 8 AWG-14 AWG Class G,H,I, DLO, 8 AWG Class K, kitted with black cover. See sale drawing for metric wire size accommodates



Application

Wire Tap

General

Catalog Number	YH298CWC
Color Code	Purple
Connector Type	H-TAP W/BLK COVER
Die Index	654
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	Compression Taps
UPC	781810000304
UPC 12 Digit	7818100003044

Dimensions

Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.90 in
Dimension - Strip Length inch	1-1/16
Dimension - Width inch	1.52 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex G Tap	14;8
Conductor - Copper Flex G Tap Range	8 AWG-14 AWG
Conductor - Copper Flex H Tap	14;8
Conductor - Copper Flex H Tap Range	8 AWG-14 AWG
Conductor - Copper Flex I Run	4/0 AWG-2 AWG
Conductor - Copper Flex I Tap	14;8
Conductor - Copper Flex I Tap Range	8 AWG-14 AWG
Conductor - Copper Flex K Run	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex K Tap	14;8
Conductor - Copper Flex K Tap Range	8 AWG
Conductor - Copper Flex M Run	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex M Tap	14;8
Conductor - Copper Str Run	2;1;1/0;2/0;3/0;4/0;250
Conductor - Copper Str Run Range	250 KCMIL-2 AWG
Conductor - Copper Str Tap	14;12;10;9;8
Conductor - Copper Str Tap Range	8 AWG-14 AWG
Conductor - Material	COPPER
Conductor Type	CODE/FLEX

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	2250

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section C - Compression](#)

[Connections](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - SD..206566-01](#)

[Specifications - YH298CWC](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YH298CWC-SPEC-EN | REV 8/2024