



YH298CWCC, Compression H-Tap, Main 250 kcmil-2 AWG, Tap #8-#14 AWG, includes clear cover

By Burndy
Catalog # [YH298CWCC](#)

Copper Compression H Tap, Tin Plated, Accommoding the following wire sizes - Run (Main): 250 kcmil-2 AWG Class B,C, 4/0 AWG-2 AWG Class I, DLO; Tap 1: 8 AWG-14 AWG Class B, C, 8 AWG-14 AWG Class G,H,I, DLO, 8 AWG Class K, Tap 2:8 AWG-14 AWG Class G,H,I, DLO, 8 AWG Class K, kitted with clear cover. See sale drawing for metric wire size accommodates

Features

- Uninsulated compression H-tap connector, tin-plated
- Designs with more than one tap wire groove require installers to utilize a minimum of one Main (Run) and one Tap groove, other grooves can be left empty
- 'Third Hand' is a string provided with the H-tap connector and is used to wrap the wire while being inserted into the run and tap grooves
- H-tap connectors can be purchased separately or kitted with covers
- YH is connector sold separately without cover
- YH-WC is kitted H-tap connector and black cover
- YH-WCC is kitted H-tap connector and clear cover

Application

Wire Tap

General

Catalog Number	YH298CWCC
Color Code	Purple
Connector Type	H-TAP W/CLR COVER
Die Index	654
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	Compression Taps
UPC	781810436448
UPC 14 Digit GTIN	00781810436448

Dimensions

Dimension - L Length Overall	23 mm
mm	



Dimension - Length Overall	0.90 in
inch	
Dimension - Strip Length inch	1-1/16
Dimension - Width inch	1.52 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex G Tap	14;8
Conductor - Copper Flex G Tap	8 AWG-14 AWG
Range	
Conductor - Copper Flex H Tap	14;8
Conductor - Copper Flex H Tap	8 AWG-14 AWG
Range	
Conductor - Copper Flex I Run	4/0 AWG-2 AWG
Conductor - Copper Flex I Tap	14;8
Conductor - Copper Flex I Tap	8 AWG-14 AWG
Range	
Conductor - Copper Flex K Run	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex K Tap	14;8
Conductor - Copper Flex K Tap	8 AWG
Range	
Conductor - Copper Flex M Run	2;1;1/0;2/0;3/0;4/0
Conductor - Copper Flex M Tap	14;8
Conductor - Copper Str Run	2;1;1/0;2/0;3/0;4/0;250
Conductor - Copper Str Run	250 KCMIL-2 AWG
Range	
Conductor - Copper Str Tap	14;12;10;9;8
Conductor - Copper Str Tap	8 AWG-14 AWG
Range	
Conductor - Material	COPPER
Conductor Type	CODE/FLEX

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1

Pallet Quantity 825

Product Assets

- Catalogs - BURNDY Master Catalog - Section C - Compression Connections
- Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
- Customer Notices - Prop 65 Notice
- Interactive Catalog - BURNDY Full-Line Digital Catalog
- Product Cross Section Image(s) - BUR_YH2929WCC_LineArt
- Sales Drawings - SD..206566-01
- Specifications - YH298CWCC

