



## YH3434WCC, Compression H-Tap, Main 500-250 kcmil, Tap 500-250 kcmil, includes clear cover

By Burndy

Catalog # [YH3434WCC](#)

Copper Compression H Tap, Tin Plated, Accommodating the following wire sizes - Run (Main): 500 KCMIL-250 KCMIL Class B,C, 373 KCMIL-4/0 AWG DLO, 350 KCMIL-4/0 AWG Class I, 4/0 AWG Class K, kitted with clear cover. See sale drawing for metric wire size accommodates

### Features

- Uninsulated compression H-tap connector, tin-plated
- Designs with more than one tap wire groove require installers to utilize a minimum of one Main (Run) and one Tap groove, other grooves can be left empty
- 'Third Hand' is a string provided with the H-tap connector and is used to wrap the wire while being inserted into the run and tap grooves
- H-tap connectors can be purchased separately or kitted with covers
- YH is connector sold separately without cover
- YH-WC is kitted H-tap connector and black cover
- YH-WCC is kitted H-tap connector and clear cover

### Application

Wire Tap

### General

Catalog Number	YH3434WCC
Color Code	Brown
Connector Type	H-TAP W/CLR COVER
Die Index	1104
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	Compression Taps
UPC	781810436479
UPC 14 Digit GTIN	00781810436479

### Dimensions

Dimension - L Length Overall	25 mm
mm	



Dimension - Length Overall	1.00 in
inch	

Dimension - Strip Length inch	1-1/8
-------------------------------	-------

Dimension - Width inch	2.43 in
------------------------	---------

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper Flex G Run	4/0;250;300;350
Conductor - Copper Flex G Tap	4/0;250;300;350
Conductor - Copper Flex H Tap	4/0;250;300;350
Conductor - Copper Flex I Run	350 KCMIL-4/0 AWG
Conductor - Copper Flex I Tap	4/0;250;300;350
Conductor - Copper Flex I Tap	350 KCMIL-4/0 AWG
Range	
Conductor - Copper Flex K Run	4/0;250;300;350
Conductor - Copper Flex K Tap	4/0;250;300;350
Conductor - Copper Flex M Run	4/0;250;300;350
Conductor - Copper Flex M Tap	4/0;250;300;350
Conductor - Copper Str Run	250;300;350;400;450;500
Conductor - Copper Str Run	500 KCMIL-250 KCMIL
Range	
Conductor - Copper Str Tap	4/0;250;300;350;400;450;500
Conductor - Copper Str Tap	500 KCMIL-4/0 AWG
Range	
Conductor - Material	COPPER
Conductor Type	CODE/FLEX

### Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B

Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	900

Product Assets

- Catalogs - BURNDY Master Catalog - Section C - Compression Connections
- Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
- Customer Notices - Prop 65 Notice
- Interactive Catalog - BURNDY Full-Line Digital Catalog
- Product Cross Section Image(s) - BUR\_YH2929WCC\_LineArt
- Sales Drawings - SD..206566-01
- Specifications - YH3434WCC



A Hubbell brand