



YH3939WCC, Cu Compression H Tap and Clear Cover, 750-500 kcmil Run, 750-350 kcmil Tap

By Burndy
Catalog # [YH3939WCC](#)



Copper Compression H Tap, Tin Plated, Accommodating the following wire sizes - Run (Main): 750 KCMIL-500 KCMIL Class B,C, 535 KCMIL-444 KCMIL DLO, 550-450 KCMIL Class I, Tap 1: 750 KCMIL-350 KCMIL Class B,C, 535 KCMIL-313 KCMIL DLO, 550-KCMIL-350 KCMIL Class I, kitted with clear cover. See sale drawing for metric wire size accommodates

Application

Wire Tap

General

Catalog Number	YH3939WCC
Color Code	Yellow
Connector Type	H-TAP W/CLR COVER
Die Index	KR
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	Compression Taps
UPC	781810436493
UPC 12 Digit	7818104364933

Dimensions

Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.25 in
Dimension - Strip Length inch	1-3/8
Dimension - Width inch	2.97 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	450;500
Conductor - Copper Flex G Tap	350;400;450;500
Conductor - Copper Flex H Tap	350;400;450;500
Conductor - Copper Flex I Run	550 KCMIL-450 KCMIL
Conductor - Copper Flex I Tap	350;400;450;500
Conductor - Copper Flex I Tap Range	550 KCMIL-350 KCMIL
Conductor - Copper Flex K Run	450;500
Conductor - Copper Flex K Tap	350;400;450;500
Conductor - Copper Flex M Run	450;500
Conductor - Copper Flex M Tap	350;400;450;500
Conductor - Copper Str Run	500;550;600;700;750
Conductor - Copper Str Run Range	750 KCMIL-500 KCMIL
Conductor - Copper Str Tap	350;400;450;500;550;600;700
Conductor - Copper Str Tap Range	750 KCMIL-350 KCMIL
Conductor - Material	COPPER
Conductor Type	CODE/FLEX

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	450

Product Assets

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

Catalogs - BURNDY Master Catalog - Section C - Compression

Connections

Customer Notices - Prop 65 Notice

Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR_YH2929WCC_LineArt

Sales Drawings - SD..206566-01

Specifications - YH3939WCC



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YH3939WCC-SPEC-EN | REV 8/2024