

Compression H-Tap

By Burndy
Catalog # [YH4434WCC](#)



Copper Compression H Tap, Tin Plated, Accommodating the following wire sizes - Run (Main): 1000 KCMIL-750 KCMIL Class B,C, 777 KCMIL-535 KCMIL DLO, 750-500 KCMIL Class I, Tap 1: 500 KCMIL-350 KCMIL Class B,C, 350 KCMIL Class I, K, kitted with clear cover. See sale drawing for metric wire size accommodates

Application

Wire Tap

General

Color Code	Yellow
Connector Type	H-TAP W/CLR COVER
Die Index	KR
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	CRIMPIT™
Type	Compression Taps
UPC	781810438299
UPC 12 Digit	7818104382999

Dimensions

Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1.00 in
Dimension - Strip Length inch	1-3/8
Dimension - Width inch	3.50 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	500;600;700
Conductor - Copper Flex G Tap	350
Conductor - Copper Flex H Tap	350
Conductor - Copper Flex I Run	750 KCMIL-500 KCMIL
Conductor - Copper Flex I Tap	350
Conductor - Copper Flex I Tap Range	350 KCMIL
Conductor - Copper Flex K Run	500;600;700
Conductor - Copper Flex K Tap	350
Conductor - Copper Flex M Run	500;600;700
Conductor - Copper Flex M Tap	350
Conductor - Copper Str Run	700;750;800;850;900;1000
Conductor - Copper Str Run Range	1000 KCMIL-750 KCMIL
Conductor - Copper Str Tap	350;400;450;500
Conductor - Copper Str Tap Range	500 KCMIL-350 KCMIL
Conductor - Material	COPPER
Conductor Type	CODE/FLEX

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	450

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD_206566-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YH4434WCC-SPEC-EN | REV 8/2023