



# YH4444WC, Compression H-Tap

By Burndy  
Catalog # [YH4444WC](#)

Copper Compression H Tap, Tin Plated, Accommodating the following wire sizes - Run (Main): 1000 KCMIL-750 KCMIL Class B,C, 777 KCMIL-535 KCMIL DLO, 750-500 KCMIL Class I, Tap 1: 777 KCMIL-535 KCMIL DLO, 750 KCMIL-350 KCMIL Class I, kitted with black cover. See sale drawing for metric wire size accommodates

## Features

- Uninsulated compression H-tap connector, tin-plated
- Designs with more than one tap wire groove require installers to utilize a minimum of one Main (Run) and one Tap groove, other grooves can be left empty
- 'Third Hand' is a string provided with the H-tap connector and is used to wrap the wire while being inserted into the run and tap grooves
- H-tap connectors can be purchased separately or kitted with covers
- YH is connector sold separately without cover
- YH-WC is kitted H-tap connector and black cover
- YH-WCC is kitted H-tap connector and clear cover

## Application

Wire Tap

## General

Catalog Number	YH4444WC
Color Code	White
Connector Type	H-TAP W/BLK COVER
Die Index	1102
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	Compression Taps
UPC	781810000342
UPC 14 Digit GTIN	00781810000342

## Dimensions

Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1.00 in
Dimension - Strip Length inch	1-1/8



Dimension - Width inch	3.38 in
------------------------	---------

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Flex G Run	500;600;700
Conductor - Copper Flex G Tap	500;600;700
Conductor - Copper Flex H Tap	500;600;700
Conductor - Copper Flex I Run	750 KCMIL-500 KCMIL
Conductor - Copper Flex I Tap	500;550;600;700
Conductor - Copper Flex I Tap Range	750 KCMIL-350 KCMIL
Conductor - Copper Flex K Run	500;600;700
Conductor - Copper Flex K Tap	500;600;700
Conductor - Copper Flex M Run	500;600;700
Conductor - Copper Flex M Tap	500;600;700
Conductor - Copper Str Run	700;750;800;850;900;1000
Conductor - Copper Str Run Range	1000 KCMIL-750 KCMIL
Conductor - Copper Str Tap	750;800;850;900;1000
Conductor - Copper Str Tap Range	1000 KCMIL-750 KCMIL
Conductor - Material	COPPER
Conductor Type	CODE/FLEX

## Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	720

Product Assets

- Catalogs - BURNDY Master Catalog - Section C - Compression Connections
- Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
- Customer Notices - Prop 65 Notice
- Interactive Catalog - BURNDY Full-Line Digital Catalog
- Sales Drawings - SD..206566-01
- Specifications - YH4444WC

