



## Compression H-Tap

By Burndy  
Catalog # YH6C6CWC

Cu H-Tap Crimpit W/Black Cover Kit, 6-10 Code & Flex(Main),  
6-14 Code & Flex(Tap), Tin Plated, Orange.



### Application

Wire Tap

### General

Color Code	Orange
Connector Type	H-TAP W/CLR COVER
Die Index	BG
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	Compression Taps
UPC	781810051047

### Electrical Ratings

Voltage Rating	35 kV
----------------	-------

### Conductor Related

Conductor - Copper Flex I Run	6 AWG-10 AWG
Conductor - Copper Flex I Tap	6 AWG-14 AWG
Conductor - Copper Str Run	6 AWG-10 AWG
Conductor - Copper Str Tap	6 AWG-14 AWG
Conductor - Material	COPPER
Conductor Type	CODE/FLEX

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	3300

### Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD..206566-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YH6C6CWC-SPEC-EN | REV 8/2023