



## YH6C6CWCC, Compression H-Tap, Main #6-#10 AWG, Tap #6-#10 AWG, includes clear cover

By Burndy  
Catalog # [YH6C6CWCC](#)



Copper Compression H Tap, Tin Plated, Accommodating the following wire sizes - Run (Main): 6 AWG-10 AWG Class B,C, 6 AWG-10 AWG Class I, DLO, Tap 1: 6 AWG-14 AWG Class B,C, 6 AWG-14 AWG Class I, DLO, kitted with clear cover. See sale drawing for metric wire size accommodates

### Application

Wire Tap

### General

Catalog Number	YH6C6CWCC
Color Code	Orange
Connector Type	H-TAP W/CLR COVER
Die Index	BG
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	Compression Taps
UPC	781810436523
UPC 12 Digit	7818104365233

### Dimensions

Dimension - L Length Overall mm	15 mm
Dimension - Length Overall inch	0.60 in
Dimension - Strip Length inch	3/4
Dimension - Width inch	0.81 in

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper Flex G Run	8;7;6
Conductor - Copper Flex G Tap	14;8;7;6
Conductor - Copper Flex H Tap	14;8;7;6
Conductor - Copper Flex I Run	6 AWG-10 AWG
Conductor - Copper Flex I Tap	14;8;7;6
Conductor - Copper Flex I Tap Range	6 AWG-14 AWG
Conductor - Copper Flex K Run	8;7;6
Conductor - Copper Flex K Tap	14;8;7;6
Conductor - Copper Flex M Run	8;7;6
Conductor - Copper Flex M Tap	14;8;7;6
Conductor - Copper Str Run	10;9;8;7;6
Conductor - Copper Str Run Range	6 AWG-10 AWG
Conductor - Copper Str Tap	14;12;10;9;8;7;6
Conductor - Copper Str Tap Range	6 AWG-14 AWG
Conductor - Material	COPPER
Conductor Type	CODE/FLEX

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	3300

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section C - Compression](#)

[Connections](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR\\_YH2929WCC\\_LineArt](#)

[Sales Drawings - SD..206566-01](#)

[Specifications - YH6C6CWCC](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YH6C6CWCC-SPEC-EN | REV 8/2024