

## YHD200J1444, Stirrup

By Burndy

Catalog # [YHD200J1444](#)

HYCRIMP™ STIRRUP.



### General

Catalog Number	YHD200J1444
Connector Type	H-Tap
Die Index	D3
Material	Aluminum
Material - Bail	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYCRIMP™
Type	Bail
UPC	781810054215
UPC 12 Digit	7818100542155

### Dimensions

Dimension - B Length fraction	1-22/25 in
Dimension - B Length inch	1.88 in
Dimension - D inch	3.00 in
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.0 in
Dimension - Pad Width inch	5.00 in

### Conductor Related

Conductor - ACSR Str Size	1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG-2/0 (6/1) Quail AWG
Conductor - AL Str Size	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Size Range	2/0 AWG-4/0 AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	16
Minimum Pack Quantity	1
Pallet Quantity	1440

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YHO100J1444\\_LineArt](#)  
[Sales Drawings - SC207318-01](#)  
[Specifications - YHD200J1444](#)