



YHO100, Aluminum Overhead Tap Connector, AL, CU, ACSR, AAAC, Steel

By Burndy
Catalog # YHO100



AL Overhead Compression Tap Connector, Accommodates:
AL, CU, ACSR, AAAC and Steel, Length: 1.25 IN.

Application

For Copper, Aluminum Or ACSR And Compact Conductors

General

Die Index	O
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYCRIMP
Trade Name	HYCRIMP™
Type	YHO
UPC	781810139004

Dimensions

Dimension - Height fraction	1-3/25 in
Dimension - Height inch	1.12 in
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.25 in
Dimension - Width fraction	7/10 in
Dimension - Width inch	0.70 in
Dimension - Width mm	18 mm

Conductor Related

Conductor - ACSR Cmpt Run	#6;4 AWG;3 AWG;#1
Conductor - ACSR Cmpt Run Range	#6-#1
Conductor - ACSR Cmpt Tap	6 AWG;4 AWG;2 AWG;1 AWG;3 AWG
Conductor - ACSR Cmpt Tap Range	6 AWG-3 AWG
Conductor - ACSR Str Run	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Run Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG
Conductor - ACSR Str Tap	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG
Conductor - AL Str Run	#6 - #1
Conductor - AL Str Run Range	#6 - #1
Conductor - AL Str Tap	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - AL Str Tap Range	6 AWG-1 AWG
Conductor - Copper Solid Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Solid Run Range	6 AWG-1 AWG
Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Solid Tap Range	6 AWG-1 AWG
Conductor - Copper Str Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Str Run Range	6 AWG-1 AWG
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Str Tap Range	6 AWG-1 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	350
Minimum Pack Quantity	25
Pallet Quantity	11550

Product Assets

- [3D Models - YHO100_MODEL-PDF](#)
- [3D Models - YHO100_MODEL-STEP](#)
- [3D Models - YHO100_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SD..073376-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YHO100-SPEC-EN | REV 8/2023