



YHO125, H-shaped Aluminum Connector

By Burndy
Catalog # [YHO125](#)

Wide Range, universal figure H shaped aluminum connector. Massive aluminum design minimizes effects of galvanic corrosion. Pre-filled with PENETROX and strip sealed to limit oxide growth and increase the life of the connection.



Application

For Copper, Aluminum Or ACSR And Compact Conductors

General

Catalog Number	YHO125
Die Index	O
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYCRIMP
Trade Name	HYCRIMP™
Type	YHO
UPC	781810139059

Dimensions

Dimension - Height fraction	1-3/20 in
Dimension - Height inch	1.15 in
Dimension - L Length Overall mm	41 mm
Dimension - Length Overall inch	1.62 in
Dimension - Width fraction	7/10 in
Dimension - Width inch	0.70 in
Dimension - Width mm	18 mm

Conductor Related

Conductor - ACSR Cmpt Run	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - ACSR Cmpt Run Range	6 AWG-1/0 AWG
Conductor - ACSR Cmpt Tap	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - ACSR Cmpt Tap Range	6 AWG-1 AWG
Conductor - ACSR Str Run	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG;1 (6/1) Robin AWG;1/0 (6/1) Raven AWG
Conductor - ACSR Str Run Range	6 (6/1) Turkey AWG-1/0 (6/1) Raven AWG
Conductor - ACSR Str Tap	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG
Conductor - AL Str Run	#6 - 1/0
Conductor - AL Str Run Range	#6 - 1/0
Conductor - AL Str Tap	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - AL Str Tap Range	6 AWG-1 AWG
Conductor - Copper Solid Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Solid Run Range	6 AWG-2/0 AWG
Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-1/0 AWG
Conductor - Copper Str Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Run Range	6 AWG-1/0
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Str Tap Range	6 AWG-1 AWG

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	50
-----------------------	----

Product Assets

[3D Models - YHO125_MODEL-IGES](#)
[3D Models - YHO125_MODEL-STEP](#)
[3D Models - YHO125_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YH_LINEART](#)
[Sales Drawings - SD..073376-01](#)
[Specifications - YHO125](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YHO125-SPEC-EN | REV 8/2024