

YHO150, Aluminum Overhead Tap Connector, AL, CU, ACSR, AAAC, Steel

By Burndy
Catalog # YHO150



AL Overhead Compression Tap Connector, Accommodates: AL, CU, ACSR, AAAC and Steel, Length: 1.50 IN.

Features

- Wide range, Universal and Reversible Figure H Shapped aluminum compression connector
- Bendable tabs secure both run and tap conductors freeing the installers hands to work with the installation tool
- Massive aluminum design minimizes corrosion due to galvanic corrosion
- Pre-filled with PENETROX Joint Compound and individually packaged
- Conductor ranges and tooling is clearly printed on connector and package

Application

For Copper, Aluminum Or ACSR And Compact Conductors

General

Catalog Number	YHO150
Die Index	O
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYCRIMP
Trade Name	HYCRIMP™
Type	YHO
UPC	781810139103

Dimensions

Dimension - Height fraction	1-3/25 in
Dimension - Height inch	1.13 in
Dimension - Height mm	28.7 mm
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - Width fraction	7/10 in
Dimension - Width inch	0.70 in
Dimension - Width mm	18 mm

Conductor Related

Conductor - ACSR Cmpt Run	2 AWG;1 AWG;1/0 AWG
Conductor - ACSR Cmpt Run Range	2 AWG-1/0 AWG
Conductor - ACSR Cmpt Tap	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - ACSR Cmpt Tap Range	6 AWG-1 AWG
Conductor - ACSR Str Run	3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG;1 (6/1) Robin AWG;1/0 (6/1) Raven AWG
Conductor - ACSR Str Run Range	3 (6/1) Swallow AWG-1/0 (6/1) Raven AWG
Conductor - ACSR Str Tap	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG
Conductor - AL Str Run	#1 - 2/0
Conductor - AL Str Run Range	#1 - 2/0
Conductor - AL Str Tap	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - AL Str Tap Range	6 AWG-1 AWG
Conductor - Copper Solid Run	1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Solid Run Range	1 AWG-2/0 AWG
Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-1/0 AWG
Conductor - Copper Str Run	3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Run Range	3 AWG-2/0 AWG
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Str Tap Range	6 AWG-1 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	350
Minimum Pack Quantity	25
Pallet Quantity	11550

Product Assets

[3D Models - YHO150_MODEL-IGES](#)
[3D Models - YHO150_MODEL-PDF](#)
[3D Models - YHO150_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YH_LINEART](#)
[Sales Drawings - SD..073376-01](#)
[Specifications - YHO150](#)



A Hubbell brand