



YHO150J1444, Stirrup

By Burndy
Catalog # YHO150J1444



HYCRIMP™ STIRRUP.

General

Connector Type	H-Tap
Die Index	O
Material	Aluminum
Material - Bail	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYCRIMP™
Type	Bail
UPC	781810053935
UPC 12 Digit	7818100539355

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.75 in
Dimension - D inch	3.00 in
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.0 in
Dimension - Pad Width inch	5.00 in

Conductor Related

Conductor - ACSR Str Size	3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG;1 (6/1) Robin AWG;1/0 (6/1) Raven AWG
Conductor - ACSR Str Size Range	3 (6/1) Swallow AWG-1/0 (6/1) Raven AWG
Conductor - AL Str Size	3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size Range	3 AWG - 2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	16
Minimum Pack Quantity	1
Pallet Quantity	2688

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YHO100J1444_LineArt](#)
[Sales Drawings - SC207318-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YHO150J1444-SPEC-EN | REV 5/2024