



Heat Shrink Locking Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [YHSA10K10LF](#)



Heat Shrink Locking Fork Terminal For 12 - 10 AWG.

Application

For Use On Copper Conductor

General

Connector Type	Locking Fork Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Heat shrink
Material	Copper
Physical Attribute - Tongue Type	Snap Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS, Heat Shrink
UPC	781810524640
UPC 12 Digit	7818105246400

Dimensions

Dimension - Bolt Size fraction	#8 - #10
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.27 in
Dimension - Pad Width inch	0.35 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size fraction	#10
Dimension - Stud Size inch	#8 - #10
Dimension - Z inch	0.29 in

Conductor Related

Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50094179](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YHSA10K10LF-SPEC-EN | REV 8/2023