



Heat Shrink Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [YHSA10K8F](#)



Heat Shrink Fork Terminal For 12 - 10 AWG.

Application

For Use On Copper Conductor

General

Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS, Heat Shrink
UPC	781810524725
UPC 12 Digit	7818105247255

Dimensions

Dimension - Bolt Size fraction	#8
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.17 in
Dimension - N inch	0.17 in
Dimension - Pad Width inch	0.35 in
Dimension - Strip Length inch	5/16
Dimension - Stud Size inch	#8

Conductor Related

Conductor - Copper Solid Size	12 AWG;11 AWG;10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_YHSA18K10F_LineArt](#)
[Sales Drawings - 50094174](#)



A proud member of the Hubbell Family.