



Heat Shrink Locking Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [YHSA18K10LF](#)



Heat Shrink Locking Fork Terminal For 22 - 18 AWG.

Application

For Use On Copper Conductor

General

Connector Type	Locking Fork Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Physical Attribute - Tongue Type	Snap Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS, Heat Shrink
UPC	781810524862

Dimensions

Dimension - Bolt Size fraction	#10
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.20 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	7/32 in
Dimension - Stud Size fraction	#10
Dimension - Z inch	0.32 in

Conductor Related

Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50094179](#)



A proud member of the Hubbell Family.