



# YHSQ18F18X02D, Heat Shrink Female Quick Disconnect For 22 - 18 AWG (.19 x .02)

By Burndy  
Catalog # [YHSQ18F18X02D](#)

Heat Shrink Female Quick Disconnect For 22 - 18 AWG (.19 x .02).



## Features

- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

## Application

For Use On Copper Conductor

## General

Catalog Number	YHSQ18F18X02D
Connector Type	Female Quick Disconnect
EU RoHS Indicator	Yes
Insulation Type	Heat Shrink
Material	Copper
Plated	Y
Plating Type	Tin Plated
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS
UPC	781810525463

## Dimensions

Dimension - B Length inch	0.17 in
Dimension - L Length Overall mm	36 mm
Dimension - Length Overall inch	1.42 in
Dimension - Pad Width inch	0.11 in
Dimension - Strip Length inch	5/16

## Conductor Related

Conductor - Copper Str Size Range	18 AWG - 22 AWG
Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

## Product Assets

- [3D Models - YHSQ18F18X02D\\_MODEL-PDF](#)
- [3D Models - YHSQ18F18X02D\\_MODEL-STEP](#)
- [3D Models - YHSQ18F18X02D\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YHSQ18F25X03\\_LineArt](#)
- [Sales Drawings - 50094214](#)