



# Heat Shrink Splice For 12 - 10 AWG

By Burndy  
Catalog # [YHSS10BG10](#)



Heat Shrink Splice For 12 - 10 AWG.

## General

Connector Type	Seamless Butt Splice
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
UPC	781810486634

## Dimensions

Dimension - Length Overall inch	1.60 in
------------------------------------	---------

## Conductor Related

Conductor - Copper Solid Size	12;11;10
Conductor - Copper Solid Size Range	12-10
Conductor - CopperWeld C Solid Size	12;10
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"><li>CU C Solid-Size</li><li>CU C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	5
-----------------------	---

## Product Assets

[Sales Drawings - 10104489](#)



A proud member of the Hubbell Family.