



# Heat Shrink Splice For 22 - 18 AWG

By Burndy  
Catalog # [YHSS18](#)



Heat Shrink Splice For 22 - 18 AWG.

## Application

For Use On Copper Conductor

## General

Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS, Heat Shrink
UPC	781810476895

## Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - Strip Length inch	5/16

## Conductor Related

Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Packaging Type	Bag

## Product Assets

[3D Models - YHSS18\\_MODEL-PDF](#)  
[3D Models - YHSS18\\_MODEL-IGES](#)  
[3D Models - YHSS18\\_MODEL-STEP](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50094203](#)



A proud member of the Hubbell Family.