



Heat Shrink Splice For 22 - 18 AWG

By Burndy
Catalog # [YHSS18BG10](#)



Heat Shrink Splice For 22 - 18 AWG.

General

Connector Type	Seamless Butt Splice
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
UPC	781810486672

Dimensions

Dimension - Length Overall inch	1.50 in
------------------------------------	---------

Conductor Related

Conductor - Copper Solid Size	20;18
Conductor - Copper Solid Size Range	20-18
Conductor - CopperWeld C Solid Size	20;18
Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 10104489](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YHSS18BG10-SPEC-EN | REV 5/2024