



YKA34CA2N, Cast Aluminum Disconnectable Terminal

By Burndy
Catalog # [YKA34CA2N](#)



Cast Al Disconnectable Terminal, 397.5 (26-7, 30-7) 477 (18-1) kcmil ACSR, 500 (19, 37) kcmil Cu, 477 (19, 37) 500 (37, 61) kcmil Al, Flat Sided Brll.

General

Connector Type	Terminal
Die Index	352;579
Material	Aluminum
Physical Attribute - Pad Configuration	Straight
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810017036
UPC 12 Digit	7818100170366

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - Bolt Size fraction	1/2
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - Pad Width inch	1.90 in
Dimension - Thread Size	1/2

Conductor Related

Conductor - AAAC 5005 Size	465.4 (19) kcmil;559.5 (19) kcmil
Conductor - AAAC 5005 Size Range	465.4 (19) kcmil-559.5 (19) kcmil
Conductor - AAAC 6201 Size	465.4 (19) kcmil;559.5 (19) kcmil
Conductor - AAAC 6201 Size Range	465.4 (19) kcmil-559.5 (19) kcmil
Conductor - ACSR Str Size	397.5 (26/7) Ibis kcmil;397.5 (30/7) Larkspur kcmil;477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Size Range	397.5 (26/7) Ibis kcmil-477.0 (18/1) Pelican kcmil
Conductor - AL Str Size	477 kcmil;500 kcmil
Conductor - AL Str Size Range	477 kcmil-500 kcmil
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD051205](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YKA34CA2N-SPEC-EN | REV 8/2023