



YKA361R2N, Disconnectable Terminal w/Fixed Hardware

By Burndy
Catalog # [YKA361R2N](#)



Disconnectable Terminal (With Fixed Hardware), 397.5 (26-7, 30-7) 477 (18-1) ACSR 477 (19, 37) 500 (37, 61) Al, 7-1/4 in L.

Application

For Copper, Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors And Making Disconnectable Tap Or Jumper Connections

General

Connector Type	Terminal
Construction Material - Main	Aluminum
Die Index	M;317
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum
Physical Attribute - Pad Configuration	Straight
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYLUG
Type	YKA-R-2N, Disconnectable
UPC	781810017067

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	184 mm
Dimension - Length Overall inch	7.25 in
Dimension - Outside Diameter inch	1.24 in
Dimension - Pad Width inch	1.90 in

Conductor Related

Conductor - ACSR Str Size	397.5 (26/7) Ibis kcmil;397.5 (30/7) Larkspur kcmil;477.0 (18/1) Pelican kcmil
Conductor - AL Str Size	477 kcmil;500 kcmil
Conductor - AL Str Size Range	477 kcmil-500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - YKA361R2N_MODEL-STEP](#)
[3D Models - YKA361R2N_MODEL-PDF](#)
[3D Models - YKA361R2N_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD051205](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YKA361R2N-SPEC-EN | REV 8/2023