



YKA37R2N, Disconnectable Terminal w/Fixed Hardware

By Burndy
Catalog # [YKA37R2N](#)

Disconnectable Terminal (With Fixed Hardware), 477 (24-7, 26-7, 30-7) ACSR 556.5 (19, 37) Al, 7-3/8 in L.



Application

For Copper, Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors And Making Disconnectable Tap Or Jumper Connections

General

Connector Type	Terminal
Die Index	M
EU RoHS Indicator	Yes
Material	Aluminum
Physical Attribute - Pad Configuration	Straight
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYLUG
Type	YKA-R-2N, Disconnectable
UPC	781810017043

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	187 mm
Dimension - Length Overall inch	7.375 in
Dimension - Pad Width inch	1.90 in

Conductor Related

Conductor - ACSR Str Size	477.0 (24/7) Flicker kcmil;477.0 (26/7) Hawk kcmil;477. (30/7) Hen kcmil
Conductor - AL Str Size	556 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD051205](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YKA37R2N-SPEC-EN | REV 8/2023