

YKA4C2N, Copper Disconnectable Terminal w/Fixed Hardware

By Burndy
Catalog # [YKA4C2N](#)



HYLUG™, Copper Disconnectable Compression Terminal, With Fixed H/W, 2 Holes, #4 STR Cu, 1/2" Stud.

General

Catalog Number	YKA4C2N
Connector Type	Terminal
Die Index	163
Material	Copper
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810185988

Dimensions

Dimension - B Length fraction	1-4/57 in
Dimension - B Length inch	1.07 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	129 mm
Dimension - Length Overall inch	5.06 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.5 in
Dimension - Pad Width inch	0.88 in
Dimension - Strip Length inch	1- 3/16 in
Dimension - Stud Size inch	1/2 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	4 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	2400

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YKA342_LineArt](#)
[Sales Drawings - sd053051-01](#)
[Specifications - YKA4C2N](#)