



# YNA32R154N, ACSR, ACAR, Aluminum Terminal

By Burndy  
Catalog # [YNA32R154N](#)

Compression terminal used for ACSR, ACAR and Stranded aluminum cable, 15 Degree connector.



## General

Connector Type	Terminal
Die Index	717
Material	Aluminum
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810491317
UPC 12 Digit	7818104913177

## Dimensions

Dimension - L Length Overall mm	233 mm
Dimension - Length Overall inch	9.16 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.68 in

## Conductor Related

Conductor - ACAR Str Size	400 (19)
Conductor - ACSR Str Size	300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - AL Str Size	336.4;350

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YNA32R154N-SPEC-EN | REV 8/2023