

YNA36R15, ACSR - 15 Degree Compression Terminal

By Burndy
Catalog # [YNA36R15](#)



HYLUG™, Aluminum Compression terminal for ACSR and Stranded aluminum cable, 477 Kcmil ACSR, 500-556.5 Kcmil Aluminum cable, 15 Degree, Die Index 720.

General

Catalog Number	YNA36R15
Connector Type	Terminal
Die Index	720
Material	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810180211
UPC 12 Digit	7818101802111

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	244 mm
Dimension - Length Overall inch	9.62 in
Dimension - Length Side A inch	9.62 in
Dimension - Length Side B inch	9.47 in
Dimension - Outside Diameter inch	1.41 in
Dimension - Pad Width inch	1.96 in
Dimension - Width fraction	1.96 in

Conductor Related

Conductor - ACSR Str Size	477.0 (24/7) Flicker kcmil;477.0 (26/7) Hawk kcmil
Conductor - ACSR Str Size Range	477.0 (24/7) Flicker kcmil-477.0 (26/7) Hawk kcmil
Conductor - AL Str Size	500;550;556.5
Conductor - AL Str Size Range	500-556.5

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	15
Minimum Pack Quantity	1
Pallet Quantity	1350

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YNA-R15-2_LINEART_BW](#)
[Sales Drawings - SD..064927-01](#)
[Specifications - YNA36R15](#)