



YNA39R4N, ACSR - Compression Terminal

By Burndy
Catalog # [YNA39R4N](#)



HYLUG™, Aluminum Compression Terminal, 556.5 Kcmil ACSR, 600-650 Kcmil Aluminum, 634.9-653.1 Kcmil ACAR, 230 Kv, 722 Index.

General

Catalog Number	YNA39R4N
Connector Type	Terminal
Die Index	722
Material	Aluminum
Material Type - Sleeve	Aluminum
Physical Attribute - Pad	Straight
Orientation	
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810042465
UPC 12 Digit	7818100424655

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	248 mm
Dimension - Length Overall inch	9.76 in
Dimension - Outside Diameter inch	1.56 in
Dimension - Pad Width inch	3 in
Dimension - Width fraction	3.00 in

Conductor Related

Conductor - ACAR Str Size	634.9 - 653.1 KCMIL
Conductor - ACAR Str Size Range	634.9 - 653.1 KCMIL
Conductor - ACSR Str Size	556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-556.5 (30/7) Eagle kcmil
Conductor - AL Str Size	600 kcmil;636 kcmil;650 kcmil
Conductor - AL Str Size Range	600 kcmil-650 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	1008

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50009455](#)
[Specifications - YNA39R4N](#)