

YNA39RT15H, Aluminum Terminal, 15° Angle

By Burndy
Catalog # [YNA39RT15H](#)



HYLUG™, Aluminum Compression Terminal, ACCOM: 634.9-653.1 kcmil ACAR 556.5 kcmil ACSR 600 - 650 kcmil AL, Extra high voltage applications, Cable to Flat, 15 Deg, Terminal available with H/W.

General

Catalog Number	YNA39RT15H
Connector Type	Terminal
Die Index	722
Material	Aluminum
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	Y
UPC	781810136775
UPC 14 Digit GTIN	00781810136775

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	255 mm
Dimension - Length Overall inch	10.02 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Pad Width inch	2.08 in
Dimension - Width fraction	2.08 in

Conductor Related

Conductor - ACAR Str Size	634.9 - 653.1 KCMIL
Conductor - ACAR Str Size Range	634.9 - 653.1 KCMIL

Conductor - ACSR Str Size	556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-556.5 (30/7) Eagle kcmil
Conductor - AL Str Size	600 kcmil;636 kcmil;650 kcmil
Conductor - AL Str Size Range	600 kcmil-650 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	15
Minimum Pack Quantity	1
Pallet Quantity	1350

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD..064930-01](#)
[Specifications - YNA39RT15H](#)