



# YNA39RTH, Aluminum Terminal

By Burndy  
Catalog # [YNA39RTH](#)

Aluminum Compression terminal, 556.5 kcmil, 345 kV.



## General

Connector Type	Terminal
Die Index	722
Material	Aluminum
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810055014
UPC 12 Digit	7818100550144

## Dimensions

Dimension - L Length Overall mm	256 mm
Dimension - Length Overall inch	10.09 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Pad Width inch	2.08 in

## Conductor Related

Conductor - ACSR Str Size	477.0 (18/1) Pelican;477.0 (24/7) Flicker;477.0 (26/7) Hawk;477.0 (30/7) Hen
Conductor - ACSR Str Size Range	477.0 (18/1) Pelican-477.0 (30/7) Hen
Conductor - AL Str Size	500;550;556.5
Conductor - AL Str Size Range	500-556.5

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	15
Minimum Pack Quantity	15
Pallet Quantity	1350

## Product Assets

[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YNA39RTH-SPEC-EN | REV 8/2023