

# YNA43RT15, Aluminum Terminal, 15° Angle

By Burndy  
Catalog # [YNA43RT15](#)



Compression terminal used for ACSR, ACAR and Stranded aluminum cable, 15 Degree terminal.

## General

Catalog Number	YNA43RT15
Connector Type	Terminal
Die Index	724
Material	Aluminum
Physical Attribute - Pad	15 Degree
Orientation	
Trade Name	HYLUG™
UPC	781810485194
UPC 12 Digit	7818104851944

## Dimensions

Dimension - L Length Overall mm	259 mm
Dimension - Length Overall inch	10.21 in
Dimension - Length Side A inch	10.21 in
Dimension - Length Side B inch	10.32 in
Dimension - Outside Diameter inch	1.61 in
Dimension - Pad Width inch	3.22 in
Dimension - Width fraction	3.22 in

## Conductor Related

Conductor - ACSR Str Size	605 (24/7) Peacock kcmil;605 (26/7) Squab kcmil;605 (30/19) Teal kcmil;636 (24/7) Rook kcmil;636 (26/7) Grosbeak kcmil;636 (30/19) Egret kcmil;666.6 (24/7) Flamingo kcmil
Conductor - ACSR Str Size Range	605 (24/7) Peacock kcmil-666.6 (24/7) Flamingo kcmil
Conductor - AL Str Size	700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
Conductor - AL Str Size Range	700 kcmil-800 kcmil

## Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

## Logistics

Minimum Pack Quantity	3
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section I - Transmission Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YNA-RT15-2\\_LINEART\\_BW](#)
- [Sales Drawings - SD..064930-01](#)
- [Specifications - YNA43RT15](#)