



# YNA451R, ACSR - Compression Terminal

By Burndy  
Catalog # [YNA451R](#)

HYLUG™, Aluminum Compression Terminal, 4 Hole, 715.5-874.5 kcmil, 840.2-927.2 kcmil(ACAR), 795-1000 kcmil(Al), 230 kV, 725 Index.



## General

Connector Type	Terminal
Die Index	725
Material	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810104071
UPC 12 Digit	7818101040711

## Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	261 mm
Dimension - Length Overall inch	10.28 in
Dimension - Outside Diameter inch	1.8 in
Dimension - Pad Width inch	3.22 in
Dimension - Width fraction	3.22 in

## Conductor Related

Conductor - ACAR Str Size	840.2 - 927.2
Conductor - ACAR Str Size Range	840.2 - 927.2
Conductor - ACSR Str Size	715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard;874.5 (54/7) Crane
Conductor - ACSR Str Size Range	715.5 (54/7) Crow-874.5 (54/7) Crane
Conductor - AL Str Size	795.5;800;874.5;900;954;1000
Conductor - AL Str Size Range	795.5-1000

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	900

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - sd062922-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YNA451R-SPEC-EN | REV 8/2023