



YNA451RT15, ACSR - 15 Degree Compression Terminal

By Burndy
Catalog # [YNA451RT15](#)



HYLUG™, Aluminum Compression Terminal for EHV Applications,
Conductor: 715.5-874.5 Kcmil ACSR, 795-1000 Kcmil Alum.,
840.2-927.2 Kcmil ACSR.

General

Catalog Number	YNA451RT15
Connector Type	Terminal
Die Index	725
Material	Aluminum
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016459
UPC 12 Digit	7818100164599

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	271 mm
Dimension - Length Overall inch	10.65 in
Dimension - Length Side A inch	10.65 in
Dimension - Length Side B inch	10.57 in
Dimension - Outside Diameter inch	1.8 in
Dimension - Pad Width inch	3.22 in
Dimension - Width fraction	3.22 in

Conductor Related

Conductor - ACAR Str Size	840.2 KCMIL - 927.2 KCMIL
Conductor - ACAR Str Size Range	840.2 KCMIL - 927.2 KCMIL
Conductor - ACSR Str Size	715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard;874.5 (54/7) Crane
Conductor - ACSR Str Size Range	715.5 (54/7) Crow-874.5 (54/7) Crane
Conductor - AL Str Size	795.5;800;874.5;900;954;1000
Conductor - AL Str Size Range	795.5-1000

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	24
Pallet Quantity	540

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YNA-RT15-2_LINEART_BW](#)
[Sales Drawings - SD..064930-01](#)
[Specifications - YNA451RT15](#)



A Hubbell brand