



# YNA49R15H, Aluminum Terminal, 15° Angle

By Burndy  
Catalog # [YNA49R15H](#)

Comprsn Terminal For ACSR,ACAR and std Al Cable with  
Hardware Kit, 727 Index.



## General

Connector Type	Terminal
Die Index	727
Material	Aluminum
Material Type - Sleeve	Aluminum
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810055243
UPC 12 Digit	7818100552433

## Dimensions

Dimension - L Length Overall mm	263 mm
Dimension - Length Overall inch	10.35 in
Dimension - Outside Diameter inch	1.97 in
Dimension - Pad Width inch	3.22 in

## Conductor Related

Conductor - ACAR Str Size	950 (37);1000 (61);1100 (61);1200 (61)
Conductor - ACAR Str Size Range	950 (37)-1200 (61)
Conductor - ACSR Str Size	900 (54/7) Canary;954 (54/7) Cardinal;1033.5 (54/7) Curlew;1113 (54/19) Finch
Conductor - ACSR Str Size Range	900 (54/7) Canary-1113 (54/19) Finch
Conductor - AL Str Size	1033.5;1100;1192.5;1200;1272.2
Conductor - AL Str Size Range	1033.5-1272.2

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	500

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 10083992](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YNA49R15H-SPEC-EN | REV 8/2023