



YNA49RTDT, Aluminum Terminal, 4-hole

By Burndy
Catalog # [YNA49RTDT](#)

HYLUG™, Aluminum Compression terminal, 900-1113 Kcmil ACSR,1033.5-1272 Kcmil Alum.,983.1-1198 Kcmil ACAR, Cable to flat, 4 hole.



General

| | |
|--------------------------------------|---------------|
| Connector Type | Terminal |
| Die Index | 727 |
| Material | Aluminum |
| Physical Attribute - Pad Orientation | Straight |
| Prefilled Oxide Inhibitor | Y |
| Trade Name | HYLUG™ |
| UPC | 781810330609 |
| UPC 12 Digit | 7818103306099 |

Dimensions

| | |
|--|----------|
| Dimension - Bolt Hole Size inch | 0.56 in |
| Dimension - E Spacing between Holes fraction | 1-3/4 in |
| Dimension - L Length Overall mm | 274 mm |
| Dimension - Length Overall inch | 10.77 in |
| Dimension - Outside Diameter inch | 1.97 in |
| Dimension - Pad Width inch | 3.22 in |
| Dimension - Width fraction | 3.22 in |

Conductor Related

| | |
|---------------------------------|---|
| Conductor - ACAR Str Size Range | 983.1 KCMIL - 1198 KCMIL |
| Conductor - ACAR Str Size Range | 983.1 KCMIL - 1198 KCMIL |
| Conductor - ACSR Str Size Range | 900 (54/7) Canary;954 (54/7) Cardinal;1033.5 (54/7) Curlew;1113 (54/19) Finch |
| Conductor - ACSR Str Size Range | 900 (54/7) Canary-1113 (54/19) Finch |
| Conductor - AL Str Size Range | 1033.5;1100;1192.5;1200;1272.2 |
| Conductor - AL Str Size Range | 1033.5-1272.2 |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|-----|
| Carton Quantity | 8 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 720 |

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..058036-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YNA49RTDT-SPEC-EN | REV 8/2023