



# YNA52RT15HSS, Aluminum Terminal with Stainless Steel Hardware, 30° Angle

By Burndy  
Catalog # [YNA52RT15HSS](#)



HYLUG™, Aluminum Compression Terminal, 1113.54-1351.5 Kcmil ACSR, 1351.5-1510 Kcmil Alum., 1277-1280 Kcmil ACAR, Cable to Flat, 15 Deg, Stainless Steel H/W.

## General

|                                      |               |
|--------------------------------------|---------------|
| Connector Type                       | Terminal      |
| Die Index                            | 728           |
| Material                             | Aluminum      |
| Physical Attribute - Pad Orientation | 15 Degree     |
| Prefilled Oxide Inhibitor            | Y             |
| Trade Name                           | HYLUG™        |
| UPC                                  | 781810164013  |
| UPC 12 Digit                         | 7818101640133 |

## Dimensions

|  |          |
|--|----------|
| Dimension - Bolt Hole Size inch              | 0.56 in  |
| Dimension - E Spacing between Holes fraction | 1-3/4 in |
| Dimension - L Length Overall mm              | 321 mm   |
| Dimension - Length Overall inch              | 12.62 in |
| Dimension - Outside Diameter inch            | 2.25 in  |
| Dimension - Pad Width inch                   | 3.22 in  |
| Dimension - Width fraction                   | 3.22 in  |

## Conductor Related

|                                 |  |
|---------------------------------|--|
| Conductor - ACAR Str Size       | 1277 KCMIL- 1280 KCMIL   |
| Conductor - ACAR Str Size Range | 1277 KCMIL- 1280 KCMIL   |
| Conductor - ACSR Str Size       | 1113 (54/19) Finch; 1272 (54/19) Pheasant; 1351.5 (54/19) Martin |
| Conductor - ACSR Str Size Range | 1113 (54/19) Finch; 1272 (54/19) Pheasant; 1351.5 (54/19) Martin |
| Conductor - AL Str Size         | 1351.5; 1400; 1431.0; 1500                                       |
| Conductor - AL Str Size Range   | 1351.5-1500  |

## Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

## Logistics

|                       |     |
|-----------------------|-----|
| Carton Quantity       | 5   |
| Minimum Pack Quantity | 1   |
| Pallet Quantity       | 450 |

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD..064930-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YNA52RT15HSS-SPEC-EN | REV 8/2023