



YNA52RT30, Aluminum Terminal, 30° Angle

By Burndy
Catalog # [YNA52RT30](#)



Aluminum Compression terminal, 1113-1351.5 kcmil, 345 kV.

General

Catalog Number	YNA52RT30
Connector Type	Terminal
Die Index	728
Material	Aluminum
Physical Attribute - Pad Orientation	30 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810046272
UPC 12 Digit	7818100462722

Dimensions

Dimension - B Length inch	6.36 in
Dimension - L Length Overall mm	308 mm
Dimension - Length Overall inch	12.11 in
Dimension - Outside Diameter inch	2.25 in
Dimension - Pad Width inch	3.22 in

Conductor Related

Conductor - ACSR Str Size	1113 (54/19) Finch;1272 (54/19) Pheasant
Conductor - ACSR Str Size Range	1113 (54/19) Finch-1272 (54/19) Pheasant
Conductor - AL Str Size	1351.5;1400;1431.0;1500
Conductor - AL Str Size Range	1351.5-1500

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	450

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - YNA52RT30](#)