



YNA54RT, ACSR - Compression Terminal

By Burndy
Catalog # [YNA54RT](#)



HYLUG™, Al Tube Compression Terminal, 4 Holes, 1431 Kcmil ACSR, 1590 - 1600 Kcmil Al, 1534 Kcmil ACAR, greater than 230 kV, 1.75" Spacing.

General

Catalog Number	YNA54RT
Connector Type	Terminal
Die Index	728
Material	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016398
UPC 12 Digit	7818100163988

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	350 mm
Dimension - Length Overall inch	13.79 in
Dimension - Outside Diameter inch	2.25 in
Dimension - Pad Width inch	3.22 in
Dimension - Width fraction	3.22 in

Conductor Related

Conductor - ACAR Str Size	1534 KCMIL
Conductor - ACAR Str Size Range	1534 KCMIL
Conductor - ACSR Str Size	1431 (54/19) Plover
Conductor - ACSR Str Size Range	1431 (54/19) Plover
Conductor - AL Str Size	1590 kcmil - 1600 kcmil
Conductor - AL Str Size Range	1590 kcmil - 1600 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	450

Product Assets

- [3D Models - YNA54RT_MODEL-IGES](#)
- [3D Models - YNA54RT_MODEL-PDF](#)
- [3D Models - YNA54RT_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YNA-RT15-2_LINEART_BW](#)
- [Sales Drawings - SD..058036-01](#)
- [Specifications - YNA54RT](#)



A Hubbell brand