

YNA56R, ACSR - Compression Terminal

By Burndy
Catalog # [YNA56R](#)



HYLUG™, Al Compression Terminal for ACSR, ACAR & SAC Cables, 1510.5-1590 Kcmil ACSR, 1700-1800 Kcmil SAC, 1650 Kcmil ACAR, 250 Kv Max., 12.50 IN L, 4 hole.

General

Catalog Number	YNA56R
Connector Type	Terminal
Die Index	729
Material	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810491300
UPC 12 Digit	7818104913000

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	324 mm
Dimension - Length Overall inch	12.74 in
Dimension - Outside Diameter inch	2.5 in
Dimension - Pad Width inch	3.44 in
Dimension - Width fraction	3.44 in

Conductor Related

Conductor - ACAR Str Size	1650 KCMIL
Conductor - ACAR Str Size Range	1650 KCMIL
Conductor - ACSR Str Size	1590 (54/19) Falcon
Conductor - ACSR Str Size Range	1590 (54/19) Falcon
Conductor - AL Str Size	1700;1750;1800
Conductor - AL Str Size Range	1700 KCMIL -1800 KCMIL

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	540

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd062922-01](#)
- [Specifications - YNA56R](#)