



## YNA56RT15, ACSR - 15 Degree Compression Terminal

By Burndy  
Catalog # [YNA56RT15](#)



HYLUG™, Al Compression Terminal, 1510.5-1590 Kcmil ACSR, 1700-1800 Kcmil Aluminum, 1650 Kcmil ACAR, 4 Pad Holes, 345 Kv, Extra High Voltage Applications, 15 Degree.

### General

Catalog Number	YNA56RT15
Connector Type	Terminal
Die Index	729
Material	Aluminum
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810081532
UPC 12 Digit	7818100815322

### Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	339 mm
Dimension - Length Overall inch	13.36 in
Dimension - Length Side A inch	13.36 in
Dimension - Length Side B inch	13.76 in
Dimension - Outside Diameter inch	2.5 in
Dimension - Pad Width inch	3.44 in
Dimension - Width fraction	3.44 in

### Conductor Related

Conductor - ACAR Str Size	1650 KCMIL (42/19 STR)
Conductor - ACAR Str Size Range	1650 KCMIL (42/19 STR)
Conductor - ACSR Str Size	1510.5 (45/7) Nuthatch kcmil;1590 (45/7) Lapwing kcmil;1590 (54/19) Falcon kcmil
Conductor - ACSR Str Size Range	1510.5 (45/7) Nuthatch kcmil-1590 (54/19) Falcon kcmil
Conductor - AL Str Size	1700 KCMIL -1800 KCMIL
Conductor - AL Str Size Range	1700 KCMIL -1800 KCMIL

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	450

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section I - Transmission](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YNA-RT15-2\\_LINEART\\_BW](#)  
[Sales Drawings - SD..064930-01](#)  
[Specifications - YNA56RT15](#)



A Hubbell brand