

YNA594R, ACSR - Compression Terminal

By Burndy
Catalog # [YNA594R](#)



HYLUG™, Al Tube Compression Terminal, 4 Holes, 2300 Kcmil ACSR, 2500 Kcmil Al, 2267-2500 Kcmil ACAR, 1.75" Spacing.

General

| | |
|--------------------------------------|---------------|
| Catalog Number | YNA594R |
| Connector Type | Terminal |
| Die Index | 740 |
| Material | Aluminum |
| Physical Attribute - Pad Orientation | Straight |
| Prefilled Oxide Inhibitor | Y |
| Trade Name | HYLUG™ |
| UPC | 781810180471 |
| UPC 12 Digit | 7818101804711 |

Dimensions

| | |
|--|----------|
| Dimension - Bolt Hole Size inch | 0.56 in |
| Dimension - E Spacing between Holes fraction | 1-3/4 in |
| Dimension - L Length Overall mm | 364 mm |
| Dimension - Length Overall inch | 14.35 in |
| Dimension - Outside Diameter inch | 2.6 in |
| Dimension - Pad Width inch | 3.7 in |
| Dimension - Width fraction | 3.70 in |

Conductor Related

| | |
|---------------------------------|------------------------|
| Conductor - ACAR Str Size | 2267 KCML - 2500 KCMIL |
| Conductor - ACAR Str Size Range | 2267 KCML - 2500 KCMIL |
| Conductor - ACSR Str Size | 2300 KCMIL |
| Conductor - ACSR Str Size Range | 2300 KCMIL |
| Conductor - AL Str Size | 2500 KCMIL |
| Conductor - AL Str Size Range | 2500 KCMIL |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|-----|
| Carton Quantity | 4 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 360 |

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YNA-R15-2_LINEART_BW](#)
- [Sales Drawings - sd062922-01](#)
- [Specifications - YNA594R](#)