



## YNA594RT90, Aluminum Terminal, 90° Angle

By Burndy  
Catalog # [YNA594RT90](#)



Aluminum Compression terminal, 2156-2167 kcmil, 345 kV.

### General

Catalog Number	YNA594RT90
Connector Type	Terminal
Material	Aluminum
Material Type - Sleeve	Aluminum
Physical Attribute - Pad Orientation	90 Degree Angle
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810180488
UPC 12 Digit	7818101804888

### Dimensions

Dimension - B Length inch	7.88 in
Dimension - L Length Overall mm	242 mm
Dimension - Length Overall inch	9.53 in
Dimension - Outside Diameter inch	2.6 in
Dimension - Pad Width inch	3.75 in

### Conductor Related

Conductor - ACSR Str Size	2300
Conductor - ACSR Str Size Range	2300
Conductor - AL Str Size	2500
Conductor - AL Str Size Range	2500

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	2
Minimum Pack Quantity	1
Pallet Quantity	180

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD..070287-01](#)
- [Specifications - YNA594RT90](#)