



# YNA7M9T, Alumoweld - EHS Steel Compression Terminal

By Burndy  
Catalog # [YNA7M9T](#)

Steel Compression terminal for Alumoweld and EHS Steel to dead end, 7 #9, 3 #6 Alumoweld.



## General

Connector Type	Terminal
Die Index	677
Material	Aluminum
Material Type - Sleeve	Aluminum
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
UPC	781810081549
UPC 12 Digit	7818100815499

## Dimensions

Dimension - B Length inch	2.79 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	223 mm
Dimension - Length Overall inch	8.79 in
Dimension - Outside Diameter inch	0.8 in
Dimension - Pad Width inch	1.5 in

## Conductor Related

Conductor Type	GAL Steel C Str-Size
----------------	----------------------

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	50
-----------------------	----

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - sd65301](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YNA7M9T-SPEC-EN | REV 8/2023