



YNS32RT, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS32RT](#)



HYSPLICE™, ACCOM: 300 kcmil - 336.4 KCMIL ACSR, 336.4 kcmil - 350 kcmil ALUM, 395.1 kcmil - 395.2 kcmil ACAR, INDEX: 717.

General

Catalog Number	YNS32RT
Connector Type	Splice
Die Index	717
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810515020
UPC 12 Digit	7818105150200

Dimensions

Dimension - Diameter Max Size inch	1.19 in
Dimension - L Length Overall mm	228 mm
Dimension - Length Overall inch	8.96 in
Dimension - Outside Diameter inch	1.19 in

Conductor Related

Conductor - ACAR Str Size	395.1;395.2
Conductor - ACAR Str Size Range	395.1 KCMIL - 395.2 KCMIL
Conductor - ACSR Str Size	336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - ACSR Str Size Range	336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - AL Str Size	336.4 KCMIL - 350 KCMIL
Conductor - AL Str Size Range	336.4 KCMIL - 350 KCMIL

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	2250

Product Assets

- [3D Models - YNS32RT_MODEL-PDF](#)
- [3D Models - YNS32RT_MODEL-IGES](#)
- [3D Models - YNS32RT_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD058033-01](#)
- [Specifications - YNS32RT](#)



A Hubbell brand