



YNS34R, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS34R](#)



HYSPLICE™, ACCOM: 397.5 kcmil ACSR 397.5 kcmil ALUM - 477 kcmil ALUM INDEX: 719.

General

Connector Type	Splice
Die Index	719
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810515037
UPC 12 Digit	7818105150377

Dimensions

Dimension - L Length Overall mm	220 mm
Dimension - Length Overall inch	8.68 in
Dimension - Outside Diameter inch	1.3 in

Conductor Related

Conductor - ACSR Str Size	397.5 (26/7) lbis kcmil
Conductor - ACSR Str Size Range	397.5 (26/7) lbis kcmil
Conductor - AL Str Size	397.5 KCMIL - 477 KCMIL
Conductor - AL Str Size Range	397.5 KCMIL - 477 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	30
Minimum Pack Quantity	1
Pallet Quantity	2700

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd062800-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YNS34R-SPEC-EN | REV 8/2023