



YNS36R, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS36R](#)



HYSPLICE™, AL Tube jumper loop sleeve for ACAR and Stranded Aluminum conductor, 500-556.5 Kcmil AL, 477 Kcmil ACSR, 230 kV.

General

Connector Type	Splice
Die Index	720
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810097465
UPC 12 Digit	7818100974655

Dimensions

Dimension - L Length Overall mm	234 mm
Dimension - Length Overall inch	9.2 in
Dimension - Outside Diameter inch	1.41 in

Conductor Related

Conductor - ACSR Str Size	477 KCMIL
Conductor - ACSR Str Size Range	477 KCMIL
Conductor - AL Str Size	500 KCMIL - 556.5 KCMIL
Conductor - AL Str Size Range	500 KCMIL - 556.5 KCMIL

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus™	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	15
Minimum Pack Quantity	1
Pallet Quantity	1350

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YNS-R_LINEART_BW](#)
[Sales Drawings - sd062800-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YNS36R-SPEC-EN | REV 5/2024