



YNS39R, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS39R](#)



HYSPLICE™, AL Tube jumper loop sleeve for ACAR and Stranded Aluminum conductor, 634.9-653.1 Kcmil ACAR, 600-650 Kcmil AL, 556.5 Kcmil ACSR, ?230 kV.

General

Connector Type	Splice
Die Index	722
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810085851
UPC 12 Digit	7818100858511

Dimensions

Dimension - L Length Overall mm	248 mm
Dimension - Length Overall inch	9.76 in
Dimension - Outside Diameter inch	1.50 in

Conductor Related

Conductor - ACAR Str Size Range	556.5 KCMIL
Conductor - ACSR Str Size	556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-556.5 (26/7) Dove kcmil
Conductor - AL Str Size	600 kcmil - 650 kcmil
Conductor - AL Str Size Range	600 kcmil-650 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus™	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	15
Minimum Pack Quantity	1
Pallet Quantity	1350

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd062800-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YNS39R-SPEC-EN | REV 8/2023