



# YNS43R, ACSR - Jumper Loop Sleeve

By Burndy  
Catalog # [YNS43R](#)



HYSPLICE™ Jumper Loop Sleeve, Al Tube, 605 - 666.6 kcmil ACSR, 700 - 800 kcmil Al, 230 kV, 9.98" L, 724 Index.

## General

Connector Type	Splice
Die Index	724
Material	Aluminum
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810016121
UPC 12 Digit	7818100161211

## Dimensions

Dimension - L Length Overall mm	253 mm
Dimension - Length Overall inch	9.98 in
Dimension - Outside Diameter inch	1.61 in

## Conductor Related

Conductor - ACSR Str Size	605 (24/7) Peacock kcmil;605 (26/7) Squab kcmil;605 (30/19) Teal kcmil;636 (24/7) Rook kcmil;636 (26/7) Grosbeak kcmil;636 (30/19) Egret kcmil;666.6 (24/7) Flamingo kcmil
Conductor - ACSR Str Size Range	605 (24/7) Peacock kcmil-666.6 (24/7) Flamingo kcmil
Conductor - AL Str Size	700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
Conductor - AL Str Size Range	700 kcmil-800 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	15
Minimum Pack Quantity	1
Pallet Quantity	1350

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - sd062800-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YNS43R-SPEC-EN | REV 8/2023